

## **Model HLS-96A SYNC**

# **Analog Synchroscope**





#### **Operation Principle**

- A synchroscope indicates the synchronization point (scale center) when the frequencies and the phases at a generator side and a bus line side are matched.
- If the frequencies of both side are equal, the position at which the needle is stationary indicates the phase difference between the two.
- When the generator side (starting side) frequency is fg and the bus line side (operating side) frequency is fb, the direction of rotation of the needle is as follows:

When fg=fb The needle is stopped

When fg>fb The needle rotates in the FAST direction When fg<fb The needle rotates in the SLOW direction

#### **Features**

- Input voltage: 120V AC or 240V AC.Square shape panel 96 x 96mm.
- 360° indication.
- PC window, ABS resin frame, PC case.
- UL # E486912


#### **Specifications**

Nominal Input Voltage: 120V AC | 240V AC Frequency Range: 60Hz or 70Hz


Scale: SLOW / FAST Indication: Moring pointer


Angle of rotation: 360°


### **Wiring Diagram**



#### **Dimensions**







## **Hoyt Electrical Instrument Works, Inc.**

23 Meter Street Penacook, NH 03303 Phone: (800) 258-3652

Fax: (603) 753-9592

Email: sales@hoytmeter.com

www.hoytmeter.com

Page 1 (1)